senseca

ECO 240

Baro-/Vacuummeter

- Modern and functional housing
- Waterproof (IP67)
- Simple universal pressure connection with interchangeable connections
- High resolution and accuracy
- Very fast!
- 3-line display / overhead display at the push of a button
- Backlight
- Robust, long battery life
- Hold-function to freeze measured values
- Min/Max-function for minimum and maximum recorded measured values
- Made in Germany



Description

When developing the ECO240 series, the focus was deliberately on the essential functions of measurement technology - a high-quality sensor is at the heart of this - the heart of the measuring device - on which no savings were made despite the low overall price!

Precision, speed and reliability, packaged in a compact and waterproof housing, make the device a reliable partner for the trade.

For fast measurement in a vacuum at ECO240-1 (VAC)

Fast and precise, for example for testing vacuum packaging machines:

Pack and evacuate the device, read the display, done. The minimum vacuum reached can also be read off after unpacking via the minimum value display. Also for monitoring vacuum potting processes.

Barometer / pressure gauge with high resolution for ECO240-2

Covers pneumatic range with 1 mbar resolution up to 14 bar! Can be used as a relative pressure measuring device (run "tare" without pressure to set device to 0) or as an absolute pressure measuring device (starts at ambient pressure e.g. 1013 mbar = 1013 hPa)

.Made in Germany.

Thanks to the optional calibration certificates, the baro/vacuum meter can serve as a perfect reference device for checking the actual accuracy of corresponding devices.



ECO 240-2 front



ECO 240

Baro-/Vacuummeter

Connection options

① UT connection for tubes 6 x 1 mm
(4 mm inner) and 8 x 1 mm (6 mm inner)

Universal port for the connection of different pressure connections..
The pressure connection is exchangeable due to 1/8 inch port!

- ② QC6 Quick-Connect connection for 6 x 1 mm (Ø 4 mm inner) tubes
- ③ ST6 screw connection for 6 x 1 mm (Ø 4 mm inner) tubes
- 4 MCM mini male quick coupling nominal diameter 2.7 (Mini quick connect coupling socket optionally available)

Please select variant when ordering. Can be changed later.





ECO 240

Baro-/Vacuummeter

Display

Thanks to the backlight, the three-line LCD display offers ergonomic wide-angle visibility - by day and by night.

The HOLD function enables the display values to be frozen.

Power supply

2 powerful AA batteries, the energy-saving design and the configurable automatic switch-off function ensure long operation.

Configurable LCD backlight for further energy saving options.

TECHNICAL DATA

Measurement specifications

	ECO240-1	ECO240-2	
Measuring range	0,0 to 1700,0 hPa (mbar)	0 to 14000 hPa (mbar)	
Pressure connection	one tube connection, interchangeab	one tube connection, interchangeable with G1/8 universal port	
Measuring	Absolute pressure	Absolute pressure	
Precision typically	± 2 hPa (@ 5 to 30 °C) Only at option -VAC @ 0 to 20 hPa: ± 1 hPa (@ 10 to 30 °C)	± 0.02 % FSS +/-0.1 % of value (@ 25 °C))	
Measuring frequency	FAST: 25 measurements per seconds	FAST: 25 measurements per seconds	
	SLO: approx 2,5 measurements per	seconds	
Error max. (-20 to 50 °C)	± 1,25 % FSS	± 0,1 % FSS ± 0,5 % of value	
Overload	3000 hPa abs.	20000 hPa abs.	
Optional special functions	I special functions NVLL: Tare function or convenient sea level setting AVR: Averaging over 2 s / 5 s / 10 s		

General specifications

Display	3-line with battery status indicator, Backlight, protected by shatterproof screen, overhead display at the push of a button	
Power supply	2 x AA-Alkaline batteries (scope of delivery)	
Power consumption	<1 mA	
Battery life	> 3000 h typ. continuous operation (without backlight)	
Automatic Power-Off	Yes, configurable by the user	
Operating conditions	-20 to +50 °C (recommended 5 to 30 °C); 0 95 % r.h. (short-term condensation possible)	
Storage temperature	-20 to 50 °C (without batteries)	
Protection class	IP67	
Dimensions	108 x 54 x 28 mm	
Weight	approx 140g	
Housing	break-proof ABS, polyester (front panel)	



ECO 240

Baro-/Vacuummeter

Scope of delivery

- Hand-held measuring device with permanently connected sensor
- 2xAA batteries
- Manual
- Test protocol

Ordering Codes

ECO240				
Baro-/Vacuummeter (earlier G 1111 & G1114)				
1	Measuring range			
	-1	0,0 to 1700,0 hPa abs.		
	-2	0 to 14000 hPa abs.		
2	Connection option			
	-UT	G1/8 inch port incl. connection for tube 6x1 mm (4 mm inner) or 8x1		
		mm (6 mm inner)		
	-QC6	G1/8 inch port incl. quick connector for tube with		
		outer-Ø 6 mm		
	-ST6	G1/8 inch port incl. screw connector for tube with		
		outer-Ø 6 mm		
	-MCM	G1/8 inch port incl. mini quick coupling plug nominal diameter 2.7		
3	Option (only ECO240-1)			
	-VAC	add. housing vent for fast complete evacuation		
4	Set-Option			
	-	Device only		
	-SET	Device, 1 m tube 6x1, case GKK 1002		





ECO 240

Baro-/Vacuummeter

Standard articles

ECO240-1-UT Vacuum / Barometer with pressure port

Pressure connection: G1/8 inch port incl. connection for tube 6x1 mm

(4 mm inner) or 8x1 mm (6 mm inner)

Set-Option: Device only

Measuring range: 0.0 ... 1700.0 hPa abs Art.Nr. 486733

ECO240-1-UT-VAC Vacuum / Barometer with pressure port

Pressure connection: G1/8 inch port incl. connection for tube 6x1 mm

(4 mm inner) or 8x1 mm (6 mm inner)

Option connection: add. housing vent for fast complete evacuation + extra

adjustment < 1 mbar Set-Option: Device only

Measuring range: 0.0 ... 1700.0 hPa abs Art.Nr. 486891

ECO240-2-UT Vacuum / Barometer with pressure port

Pressure connection: G1/8 inch port incl. connection for tube 6x1 mm

(4 mm inner) or 8x1 mm (6 mm inner)

Set-Option: Device only

Measuring range: 0 ... 14000 hPa abs Art.Nr. 486734

Accessories

Replacement parts:

GB-AA-2 Replacement batteries 2x AA Art.-Nr. 600704

Further accessories:

Rubber protection cover, incl. 2 magnets	ArtNr. 483958
Protection case, leather	ArtNr. 611373
Metal belt clip, adhesive	ArtNr. 475820
Table stand and wall suspension	ArtNr. 481885
Case	ArtNr. 611603
	Metal belt clip, adhesive Table stand and wall suspension

For further articles, please visit the Senseca website.